

# [ GLOVE SIZE CHART ]

IT IS CRUCIAL TO GET THE GLOVE SIZE RIGHT FOR MAXIMUM DEXTERITY.

HERE ARE A FEW RECOMMENDATIONS TO HELP YOU IN FINDING THE RIGHT SIZE OF GLOVES YOU NEED.



| Glove size further to EN 420 | Hand (mm)          |        | Glove (mm)     |
|------------------------------|--------------------|--------|----------------|
|                              | Palm circumference | Length | Minimum length |
| 6                            | 152                | 160    | 220            |
| 7                            | 178                | 171    | 230            |
| 8                            | 203                | 182    | 240            |
| 9                            | 229                | 192    | 250            |
| 10                           | 254                | 204    | 260            |
| 11                           | 279                | 215    | 270            |

## COLOR-CODED CUFF

Some styles of SHOWA gloves have a color-coded cuff. These cuffs enable the size recognition in the factory and the pairing after washing the gloves.

## TESTING PRIOR TO USING

If the glove is too small, it cuts off the blood circulation and restricts the movement of the hand. On the other hand, oversized gloves slip off at the slightest movement and make your handling very imprecise. To be sure of your size and fit, do not hesitate to ask for samples from your SHOWA distributor.



Place your right hand on the diagram: the green line should be between your thumb and index finger. The size is indicated on the right.