

# TruCLEAN™ 2 Compact Flat Mopping System

Simplify standard operating procedures



30-2(R,W,B)  
Compact Flat  
Mopping System

## Applications

- Small area cleaning and disinfecting of facilities with limited storage space
- Isolate contaminants from cleaning and disinfecting agents
- Compatible with TruCLEAN Sponge mops and TruCLEAN Microfiber mops

## Description

TruCLEAN 2's unique bucket-in-bucket concept features our new 36-Liter bucket, redesigned to increase stability and improve function. Perflex 36-Liter buckets have embossed graduations for accurate measure with high temperature resistant 3" casters, one locking. TruCLEAN stainless steel wringer mounts firmly to waste containment bucket, capturing soiled contaminants. Stainless steel mop frame and adjustable polymer handle included.

## Features

- Unique bucket-in-bucket concept
- Autoclavable at 121° C for 30 minutes
- Durable stainless steel wringer
- Color coded to reduce cross-contamination

## Benefits

- Ergonomic design with non-slip grip to reduce worker fatigue
- Compact design for easy storage in confined areas
- Impervious to most chemicals, will not rust, corrode or oxidize.
- Unique wringing action significantly improves release of soiled contaminants

## Product Information

Part #	Description	Material
30-36	36 Liter bucket w/3" Casters	Polypropylene
30-09	Waste Containment Bucket	Polypropylene
22-30	TruCLEAN Wringer	Type 304 Stainless Steel
22-38	TruCLEAN Mop Frame	Type 304 Stainless Steel
22-57	TruCLEAN Adjustable Handle	Polymer

## Ordering Information

Part #	Description	Carton Size (L x W x H)	Carton Weight	Packaging
30-2 (R,W,B)	TruCLEAN 2 Compact Flat Mopping System	30" x 18" x 21"	37 lbs.	1/each

Notes: Data shown reflects typical values applicable to the part numbers listed. Please contact a Perflex sales representative for more details.



32 Case Street  
Poland, NY 13431  
Tel: 800-848-8483  
315-826-3600  
Fax: 315-826-7471  
[www.PerflexOnline.com](http://www.PerflexOnline.com)  
e-mail: [perflex@perflexonline.com](mailto:perflex@perflexonline.com)

